

**Power Generation** 

**mtu** ENERGYPACK: THE SCALABLE ALL-IN-ONE SOLUTION

mtu EnergyPack









### **Multiple applications**

# OPTIMIZER, ENABLER, INTEGRATOR. STORAGE CREATES OPPORTUNITIES.

Power storage creates multiple opportunities for more efficient power production, better grid management, and increased stability and availability. Our scalable, all-in-one EnergyPack is a perfect fit for the changing energy environment, enabling existing power systems to adapt to current trends, and creating a host of possibilities when combined with renewable energy sources – aimed at creating sustainable energy systems that are in tune with the times and ready for the future.

### Grid & utility service providers

The *mtu* EnergyPack can take care of frequency regulation, manage grid congestion and allow the avoidance of significant investment in grid infrastructure, for example to enable a scale-up of electric vehicle charging. It will also make solar and wind power more reliable and instantly switchable, while enabling gas or diesel power plants to operate more efficiently when combined with the *mtu* EnergyPack.

#### Commercial

Facilities with onsite generation such as solar arrays or combined<br/>heat and power (CHP) plants can increase their own-use consumption<br/>by adding an *mtu* EnergyPack to take advantage of time-of-day<br/>electricity tariffs by shifting their power draws. If needed, backup<br/>power capability can also be provided.Where a grid connection is not reliable, the *mtu* EnergyPack<br/>increases security and quality of supply for public facilities. Stability<br/>of existing power plants can be improved by spinning reserve from<br/>the *mtu* EnergyPack, and solar arrays can be built in to reduce fuel<br/>consumption. If grid-connected, own-use of solar power can be<br/>increased to lower the amount of power drawn from the grid.

#### Industry

Remote industrial operations currently running on diesel power with no grid connections can reduce their fuel consumption and meet legal or company environmental standards more easily by integrating renewable sources with an *mtu* EnergyPack. When connected to the public grid, the *mtu* EnergyPack helps reduce power draw charges and increase own-use consumption of existing onsite generation to mitigate rising energy costs.

### Community

The *mtu* EnergyPack increases the self-sufficiency of urban areas with local power generation, and provides reliable backup power in the event of grid failure. In areas unconnected to the public grid, adding an *mtu* EnergyPack to a local microgrid ensures high quality power supplies and allows the integration of renewable energies to reduce carbon footprint and save fuel.

### Public sector

### Multiple benefits

# STORAGE SOLUTIONS FOR MICROGRIDS & ENERGY SYSTEMS

The EnergyPack is a key component for improving the reliability and profitability of microgrids and energy systems. It stores electricity from any distributed power source – such as gensets, wind turbines or solar panels – and delivers it when needed.



### Grid stabilization

The <b>mtu</b> EnergyPack is able to provide grid suppo
services and can form an autonomous grid,
enabling customers to operate independently
during grid outages.

(F)

### Highest power density

Thanks to the extremely compact battery system designs and the small footprint of the housings, the *mtu* EnergyPack is the ideal solution for projects with logistical restrictions and limited space.

ſ	ŝ	<u>)</u>

### Digitally connected

The *mtu* EnergyPack is equipped with a data logger providing access to our digital solutions, including remote monitoring, fast and reliable service support and – coming soon – further features such as predictive failure prevention and operational optimization.



୍ବି

### Multilevel safety features

A multilevel safety concept monitors and ensures safe operation of batteries, inverters and HVAC systems. The outstanding fire and explosion protection system detects smoke and explosive gases. The safety design also includes a specially designed aeration mode and an optional built-in Novec fire extinguishing system as well as optional pipework connections for flooding with water in case of fire.



The battery energy storage system (BESS) can be used as a black start unit due to its grid capability. The BESS can perform black starts without auxiliary voltage, and can form an autonomous grid.



### Scalable in size

Storage capacity and type of battery rating can easily be adapted, whatever your individual power and capacity requirements.

### Ultra-fast response

By bringing power on-stream immediately, the *mtu* EnergyPack provides essential fast response capability for power quality, black starts, frequency response, and backup applications.



### Seamless integration with existing power plants

The system can be built into existing conventional and renewable power plants, making it easy to optimize operation and preparing them for the future.



EnergyPack: The scalable all-in-one solution Power Generation





### Factory tested plug-and-play design

The *mtu* EnergyPack comes factory-tested onsite. The highly mobile, fully integrated plug-and-play design ensures fast, easy installation, reducing setup time and costs. Power is available more quickly, and at lower cost.



### Flexible use

The *mtu* EnergyPack can accept customer setpoints or be upgraded with the *mtu* microgrid controller to support various applications: storage of wind and solar power in microgrids, shaving peak loads to reduce demand charges, support for electric vehicle charging, flexibilization of generation assets, frequency and voltage regulation services, and much more.

### Versatile technology

# COMPACT, FLEXIBLE, AUTONOMOUS. INSTANT POWER WHEREVER YOU NEED IT


### Housing

06

The mtu EnergyPack is available in different sizes and different housings. The enclosed QS system and the containerized QL system are as tough as they come and have been custom-designed for harsh environments and challenging logistics. Offering superb protection from dust, insects, humidity and heat - both inside and out. The interiors of the containerized housings are divided into sections - some with outside air contact and some without - to keep the sensitive electrics and batteries protected from any pollution.


### Batteries and battery management system

The *mtu* EnergPack integrates 0.5C/1C rated high-quality cells from leading manufacturers. The battery system consists of vertical racks, scalable in number to meet the required energy capacities. Each rack



### Inverter

The inverter operates bidirectionally, converting AC from the grid into DC for charging the batteries, and vice versa. It supports both grid-supporting and grid-forming modes.



### Transformer


The transformer is the interface to the upstream power grid. Its task is A top-level battery energy storage controller (BESC), specially to transform the voltage to the level required by the inverter or grid. designed for this application, controls all aspects of the BESS, e.g. the Dependent on the *mtu* EnergyPack configuration, the transformer is inverter, batteries, HVAC system, and lighting. The BESC is located either installed inside or delivered as separate equipment for outdoor inside the control cabinet, a separate compartment within the installation container. A built-in touchscreen and simple remote access via Modbus-IP enable full control over the *mtu* EnergyPack.

### Heating, ventilation and air-conditioning system

The HVAC equipment is located inside the housing and feeds temperature and humidity-controlled air to the cleanroom, protecting The *mtu* EnergyPack features a comprehensive safety concept the sensitive electrical equipment and batteries from contact with comprising a multilevel safety architecture, fire & gas detection, fire ambient exterior conditions. The HVAC system regulates temperature extinguishing options, etc. and humidity to required levels to ensure the BESS equipment works to optimum effect.

# THE FULL POWER RANGE

EnergyPack is a key component for improving the reliability and profitability of microgrids and energy systems. It stores electricity from any distributed power source - such as gensets, wind turbines or solar panels - and delivers it when needed. The *mtu* EnergyPack is available in three sizes: QS, QL, and QG



### Control system

### Safety features

## **EnergyPack QG**

# COMPACT AND POWERFUL

The EnergyPack QG is designed for customer applications with power and capacity requirements ranging from around 4,400 kWh to 100 MWh and more.

It is a key solution to effectively integrate high shares of renewables, solar or wind, in energy systems. The scalable design focuses on a front of the meter grid scale battery energy storage system.

## **EnergyPack QL**

# LARGE AND POWERFUL

The EnergyPack QL is designed for customer applications with power and capacity requirements up to 2,000 kVA and 2,200 kWh and above. It is suitable for integrating solar assets and wind parks, and for providing frequency regulation and other ancillary services in the utilities sector.





Cell chemistry		NMC
Nominal capacity	kWh	up to 2,048
Nominal apparent power	kVA	up to 2,000
Maximum apparent power (1 min)	%	up to 110 (150)
Transformer		optional
Nominal voltage	V	450 (400 with internal transformer)
Enclosure		40ft ISO HC container
Black start capability		yes





Key technical data <i>mtu</i> EnergyPack QG		
Cell chemistry		LFP
Nominal capacity at 0.5 C	MWh	8.94
Nominal apparent power	MVA	4.39
Transformer		optional
Voltage	kV	6.6 to 34.5
Footprint of one fully assembled base unit	m	7.1 x 18
Black start capability		no






## **EnergyPack QS**

# SMALL AND STURDY

The EnergyPack QS is designed for customer applications with power and capacity requirements of up to 400 kVA and 624 kWh. It is suitable for off-grid solutions, for reducing fuel dependence in small remote communities, and for enabling own-use consumption of solar power in the commercial and public sectors.





### Key technical data mtu EnergyPack QS

Cell chemistry		NMC
Nominal capacity	kWh	up to 624
Nominal apparent power	kVA	up to 400
Maximum apparent power (1 min)	%	up to 150
Transformer		internal
Nominal voltage	V	400
Enclosure		compact housing
Black start capability		yes

### Service Solutions

# ENSURING LONG, RELIABLE SERVICE LIVES

EnergyPacks are built to deliver the highest performance with low life-cycle costs. Our maintenance services keep them performing that way with a full portfolio of service solutions.

Remote operation control and diagnostics, digital connectivity solutions and new maintenance schedules keep the life-cycle costs of the *mtu* EnergyPack to a minimum. With high availability of spare parts, we ensure your systems stay up and running, wherever in the world they happen to be, and operators can have the benefit of peace-of-mind provided by performance guarantee agreements which promise specific levels of up-time and can be tailored to fit your specific requirements.

### **Reporting & optimization**

add transparency to system performance and allow constant improvement of system parameters based on operational experience

#### Preventive & corrective maintenance

performed by trained technicians to ensure a high quality of work

#### Active monitoring

by trained personnel to identify failures in time and initiate required actions to reduce down-time

#### Remote diagnostics

by experts to identify root causes of malfunctions (3<sup>rd</sup> level support) and perform low-level configuration changes and bug-fixes

#### Local support. Worldwide. 24/7

We ensure you get tailored support from our global network of over 1,200 service centers - anytime, anywhere. Whether it's connecting you with a local service partner or assigning an urgent problem to a dedicated team of our experts, we're ready to assist - wherever you are, whatever you need.



### Repair guidance

for local personnel from experts via phone, video conference or email/mail to minimize down-time and costs

### ValueCare Agreements

make it easy to optimize lifecycle costs, maximize uptime and devote more time and resources to your core business, with tailored solutions to move your business forward

### Extended warranty cover

for mtu products, protecting against unexpected costs with a scope tailored to customer needs

Europe, Middle East & Africa +49 7541 90-7 77 77 Asia-Pacific +65 6860 9669 North and Latin America +1 248 560 8888

info@ps.rolls-royce.com

Rolls-Royce Group www.mtu-solutions.com/powergen

Y in 🖸 🔘

and follow mtusolutions under:

Stay posted with more powerful information