





## Oil & Gas

# DIESEL ENGINE 6R 1500/OM 473

for oil and gas applications  
with EPA tier 4 and EU stage IV certification



Optional equipment and finishing shown. Standard may vary.

Engine	Dimensions (LxWxH) mm (in)	Mass, dry kg (lbs)
6R 1500 C	1425 x 1005 x 1290 (56.1 x 39.6 x 50.8)	1277 (2815) <sup>1)</sup>

All dimensions are approximate, for complete information refer to the installation drawing.  
1) DIN 70020

Engine		
Bore/stroke	mm (in)	139/171 (5.5/6.7)
Cylinder configuration		6 inline
Displacement, total	l (cu in)	15.6 (952)
Fuel specification		DIN EN 590, ASTM D975 (DF1, DF2)

Engine type	Rated power			Peak torque			Fuel consumption at rated power	Fuel consumption at peak torque
	kW	bhp	rpm	Nm	lb-ft	rpm	g/kWh	g/kWh
6R 1500 C 30	400	536	1700	2600	1918	1300	190	188
6R 1500 C 50	430	576	1700	2750	2028	1300	190	188
6R 1500 C 60	460	617	1700	2900	2139	1300	190	188

Ratings acc. to ECE R 120

Emissions: EPA 40 CFR 89 / Tier 4 final  
EU Nonroad St IV (97/68/EC)  
UN ECE R96 Emission Flex Package (EFP)

Standard Equipment	Optional Equipment
24 Volt starter	Exhaust brake system
28 Volt alternator, 100 A	Aux REPTO
Common rail injection system	Air compressor
Electronic engine management	AC compressor
Electronic interface module	Flex engine mounts
Turbo charging air to air cooling	Elevated fan drive
High pressure EGR system	Cooling fan
One-box aftertreatment system with SCR incl. muffler	
Close crankcase ventilation	
SAE 1 flywheel housing	

Reference conditions:

- > Intake temperature: 25°C (77°F)
- > Charge air temperature: 40°C
- > Altitude: 200 m (656 ft)
- > Air intake restriction: 25 mbar

Subject to change without notice. Customization possible. Engines illustrated in this document may feature options not fitted as standard to standard engine.