

Gas Generator Set

mtu 8V0110 GS150

150 kWe/60 Hz/Standby/208 - 600V

System ratings

Voltage (L-L)	240V [†]	240V [†]	208V [†]	240V [†]	480V [†]	600V	380V [†]
Phase	1	1	3	3	3	3	3
PF	1	1	0.8	0.8	0.8	0.8	0.8
Hz	60	60	60	60	60	60	60
Natural Gas (NG)							
Amps	625	625	520	451	226	180	285
kW/kVA	150/150	150/150	150/187.5	150/187.5	150/187.5	150/187.5	150/187.5
Liquid Propane (LP)							
Amps	542	542	451	391	195	156	247
kW/kVA	130/130	130/130	130/162.5	130/162.5	130/162.5	130/162.5	130/162.5
NG and LP							
skVA@30% voltage Dip	196	187	296	296	394	315	282
Generator model	431PSL6224	431CSL6206	431PSL6202	431PSL6202	431PSL6202	431CSL6240	431PSL6204
Temp rise	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C
Connection	4 LEAD	12 LEAD DOUBLE DELTA	12 LEAD WYE	12 LEAD DELTA	12 LEAD WYE	4 LEAD WYE	12 LEAD WY

[†] UL 2200 offered

Note: This unit is available with a dual fuel configuration.

Certifications and standards

- Generator set is designed and manufactured in facilities certified to standards ISO 9001:2008 and ISO 14001:2004
- Seismic certification optional
 - 2018 IBC certification
 - OSHPD pre-approval
- UL 2200 optional (refer to System ratings for availability)
- CSA optional
 - CSA C22.2 No. 100
 - CSA C22.2 No. 14

- Performance Assurance Certification (PAC)
 - Generator set tested to ISO 8528-5 for transient response
 - · Verified product design, quality and performance integrity
 - All engine systems are prototype and factory tested
- Power rating
 - Accepts rated load in one step per NFPA 110



Standard features*

- Single source supplier
- Global product support
- Two (2) Year/3,000 Hour Basic Limited Warranty
- PSI 8.8L TCAC engine
 - 8.8 liter displacement
 - 4-cycle
- 3-way catalyst
- Optional fuels: LP liquid and dual fuel
- Engine-generator resilient mounted
- Complete range of accessories
- Cooling system
 - Integral set-mounted
 - Engine-driven fan

- Generator
 - Brushless, rotating field generator
 - 2/3 pitch windings
 - 300% short circuit capability
- Digital control panel(s)
 - UL recognized, CSA Certified, NFPA 110
 - Complete system metering
 - LCD display

Standard equipment*

Engine

- Air cleaner
- Oil pump
- Oil drain extension and shut-off valve
- Full flow oil filter
- Jacket water pump
- Thermostat
- Blower fan and fan drive
- Radiator unit mounted
- Electric starting motor 12V
- Governor electronic isochronous
- Base formed steel
- SAE flywheel and bell housing
- Charging alternator 12V
- Battery rack and cables
- Flexible exhaust connection
- Liquid cooled, ball bearing turbcharger
- EPA certified engine

Digital control panel(s)

- Digital metering
- Engine parameters
- Generator protection functions
- Engine protection
- SAE J1939 engine ECU communications
- Windows®-based software
- Multilingual capability
- Communications to remote annunciator
- Programmable input and output contacts
- UL recognized, CSA certified, CE approved
- Event recording
- IP 54 front panel rating with integrated gasket
- NFPA 110 compatible


Generator


- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting
- Sustained short circuit current of up to 300% of the rated current for up to 10 seconds
- Self-ventilated
- Superior voltage waveform
- Solid state, volts-per-hertz regulator
- $-\pm 1\%$ voltage regulation no load to full load
- Brushless alternator with brushless pilot exciter
- 4 pole, rotating field
- 130 °C maximum standby temperature rise
- 1-bearing, sealed
- Flexible coupling
- Full amortisseur windings
- 125% rotor balancing
- 3-phase voltage sensing
- 100% of rated load one step
- 5% maximum total harmonic distortion

Application data

Engine		Fuel consumption (NG-1000 BTU/ft ³ / L	P-2500 BTU/ft ³)
Manufacturer	PSI		NG	LPG
Model	8.8L TCAC	At 100% of power rating: m³/hr (ft³/hr)	56.2 (1,986)	19.7 (695)
Туре	4-cycle	At 75% of power rating: m³/hr (ft³/hr)	43.9 (1,549)	15.1 (534)
Aspiration	turbocharged, intercooled	At 50% of power rating: m³/hr (ft³/hr)	31.8 (1,121)	11.0 (389)
Arrangement	8-V			
Displacement: L (in³)	8.8 (535)	Cooling - radiator system		
Bore: cm (in)	11.05 (4.35)			NG and LPG
Stroke: cm (in)	11.43 (4.5)	Ambient capacity of radiator: °C (°F)		48 (118.4)*
Compression ratio	10:1	10:1 Maximum restriction of cooling air:		
Rated rpm	1,800	intake and discharge side of radiator: kl	Pa (in. H ₂ 0)	0.12 (0.5)
Engine governor	Bosch	Water pump capacity: L/min (gpm)	2	125 (33.0)
Maximum power (NG): kWm (bhp)	195.0 (261.5)	Heat rejection to coolant: kW (BTUM)		
Maximum power (LP): kWm (bhp)	171.6 (230.1)	Heat radiated to ambient: kW (BTUM)		41.1 (2,337)
Steady state frequency band ± 0		Heat rejected to charge air cooler: kW (BTUM)		13.8 (782)
Air cleaner	dry	Fan power: kW (hp)		11.9 (16.0)
Liquid capacity		* Installation of gravity exhaust louvers reduces t	he ambient capacit	y
Total oil system: L (gal)	9.0 (2.38)	of the cooling system by an additional 3 °C (5.5	°F).	
Engine jacket water capacity: L (gal)	13.4 (3.5)			
System coolant capacity: L (gal)	25.5 (6.7)	Air requirements		
				NG and LPG
Electrical		Aspirating: *m³/min (SCFM)		10.33 (365)
Electric volts DC	12	Air flow required for radiator		
Cold cranking amps under -17.8 °C (0 °F)	925	cooled unit: *m³/min (SCFM)		229.8 (8,115)
Batteries: group size	31	Remote cooled applications; air flow red	quired for	
Batteries: quantity	1	dissipation of radiated generator set he	at for a	
		maximum of 25 °F rise: *m3/min (SCFM)		211.6 (7,473)
Fuel inlet - vaporous supply				
Fuel supply connection size	2" NPT	* Air density = 1.184 kg/m³ (0.0739 lbm/ft³)		
Fuel supply pressure: mm $\rm H_2O$ (in. $\rm H_2O$)	178–279 (7–11)			
		Exhaust system		
Fuel inlet - liquid supply				NG and LPG
11 7	#6 (3/8") female SAE 45° flare	Gas temperature (stack): °C (°F)	(05) ()	649 (1,200)
Maximum fuel supply pressure: kPa (PSI)	2,150 (312)	Gas volume at stack temperature: m³/mi	n (CFM)	33.3 (1,176)
		Maximum allowable back pressure at		10.0 (: :)
		outlet of engine, before piping: kPa (in.	H ₂ O)	10.2 (41)

Weights and dimensions





Drawing above for illustration purposes only, based on standard open power 480 volt generator set. Lengths may vary with other voltages. Do not use for installation design. See website for unit specific template drawings.

System	Dimensions (LxWxH)	Weight
Open Power Unit (OPU)	2,388 x 1,137 x 1,740 mm (94 x 44.8 x 68.5 in)	1,520-1,800 kg (3,350-3,950 lb)

Weights and dimensions are based on open power units and are estimates only. Consult the factory for accurate weights and dimensions for your specific generator set.

Sound data

Unit type	Standby full load (NG)	Standby full load (LP)
Level 0 (OPU): dB(A)	86.5	86.6

Sound data is provided at 7 m (23 ft). Generator set tested in accordance with ISO 8528-10 and with infinite exhaust.

Emissions data

Fuel type	THC + NO _x	СО
Natural gas	N/A	0.22
Liquid propane	0.035	0.95

All units are in g/hp-hr and are EPA weighted cycle values.
Emission levels of the engine may vary with ambient temperature,
barometric pressure, humidity, fuel type and quality, installation
parameters, measuring instrumentation, etc. The data was obtained
in compliance with US EPA regulations.

Rating definitions and conditions

- Standby ratings apply to installations served by a reliable utility source. The standby rating is applicable to varying loads for the duration of a power outage. No overload capability for this rating. Ratings are in accordance with ISO 3046-1, BS 5514, and AS 2789. Average load factor: ≤ 85%.
- Nominal ratings at standard conditions: 25 °C and 300 meters (77 °F and 1,000 feet).
- Deration factor:
 - Consult your local *mtu* Distributor for altitude derations.
 - Consult your local *mtu* Distributor for temperature derations.

C/F = Consult Factory/*mtu* Distributor