

## Gas Generator Set

# mtu 10V0068 GS100

# 100 kWe/60 Hz/Standby/208 - 600V

## System ratings

Voltage (L-L)	240V <sup>†</sup>	240V <sup>†</sup>	208V <sup>†</sup>	240V <sup>†</sup>	480V <sup>†</sup>	600V
Phase	1	1	3	3	3	3
PF	1	1	0.8	0.8	0.8	0.8
Hz	60	60	60	60	60	60
Natural Gas (NG)						
Amps	417	417	347	301	151	120
kW/kVA	100/100	100/100	100/125	100/125	100/125	100/125
Liquid Propane (LP)						
Amps	417	417	347	301	151	120
kW/kVA	100/100	100/100	100/125	100/125	100/125	100/125
NG and LP						
skVA@30% voltage Dip	311	130	258	258	344	277
Generator model	363CSL1617	431CSL6204	362CSL1606	362CSL1606	362CSL1606	362PSL1636
Temp rise	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C
Connection	4 LEAD	12 LEAD DOUBLE DELTA	12 LEAD WYE	12 LEAD DELTA	12 LEAD WYE	4 LEAD WYE

<sup>†</sup> UL 2200 offered

Note: This unit is available with a dual fuel configuration.

#### Certifications and standards

- Generator set is designed and manufactured in facilities certified to standards ISO 9001:2008 and ISO 14001:2004
- Seismic certification optional
  - 2018 IBC certification
  - HCAI pre-approval
- UL 2200 optional (refer to System ratings for availability)
- CSA optional
  - CSA C22.2 No. 100
  - CSA C22.2 No. 14

- Performance Assurance Certification (PAC)
  - Generator set tested to ISO 8528-5 for transient response
  - · Verified product design, quality and performance integrity
  - All engine systems are prototype and factory tested
- Power rating
  - Accepts rated load in one step per NFPA 110



#### Standard features\*

- Single source supplier
- Global product support
- Two (2) Year/3,000 Hour Basic Limited Warranty
- 6.8LT engine
  - 6.8 liter displacement
  - 4-cycle
- 3-way catalyst
- Optional fuels: LP liquid and dual fuel
- Engine-generator resilient mounted
- Complete range of accessories
- Cooling system
  - Integral set-mounted
  - Engine-driven fan

- Generator
  - Brushless, rotating field generator
  - 2/3 pitch windings
  - 300% short circuit capability with optional Permanent Magnet Generator (PMG)
- Digital control panel(s)
  - UL recognized, CSA Certified, NFPA 110
  - Complete system metering
  - LCD display

#### Standard equipment\*

#### **Engine**

- Heavy duty air cleaner
- Oil pump
- Oil drain extension and shut-off valve
- Full flow oil filter
- Jacket water pump
- Thermostat
- Blower fan and fan drive
- Radiator unit mounted
- Electric starting motor 12V
- Governor electronic isochronous
- Base formed steel
- SAE flywheel and bell housing
- Charging alternator 12V
- Battery rack and cables
- Flexible exhaust connection
- Liquid cooled, ball bearing turbocharger
- EPA certified engine

#### Digital control panel(s)

- Digital metering
- Engine parameters
- Generator protection functions
- Engine protection
- SAE J1939 engine ECU communications
- Windows®-based software
- Multilingual capability
- Communications to remote annunciator
- Programmable input and output contacts
- UL recognized, CSA certified, CE approved
- Event recording
- IP 54 front panel rating with integrated gasket
- NFPA 110 compatible


#### Generator


- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting
- Sustained short circuit current of up to 300% of the rated current for up to 10 seconds
- Self-ventilated
- Superior voltage waveform
- Solid state, volts-per-hertz regulator
- ± 1% voltage regulation no load to full load
- Brushless alternator with brushless pilot exciter
- 4 pole, rotating field
- 130 °C maximum standby temperature rise
- 1-bearing, sealed
- Flexible coupling
- Full amortisseur windings
- 125% rotor balancing
- 3-phase voltage sensing
- 100% of rated load one step
- 5% maximum total harmonic distortion

# Application data

Engine		Fuel consumption (NG-1000 BTU/ft <sup>3</sup> / LP-2500 BTU/ft	3)
Manufacturer	mtu	NG	LPG
Model	6.8LT	At 100% of power rating: m <sup>3</sup> /hr (ft <sup>3</sup> /hr) 31.15 (1,100)	14.49 (511.5)
Type	4-cycle	At 75% of power rating: m³/hr (ft³/hr) 23.67 (835.9)	11.32 (400)
Aspiration	turbocharged	At 50% of power rating: m³/hr (ft³/hr) 16.2 (520.1)	8.07 (248.8)
Arrangement	10-V		
Displacement: L (in³)	6.8 (415)	Cooling - radiator system	
Bore: cm (in)	9 (3.55)		NG and LPG
Stroke: cm (in)	10.6 (4.17)	Ambient capacity of radiator: °C (°F)	50 (122)
Compression ratio	9:1	Maximum restriction of cooling air:	
Rated rpm	1,800	intake and discharge side of radiator: kPa (in. H <sub>2</sub> 0)	
Engine governor	Bosch	Water pump capacity: L/min (gpm)	123 (32.5)
Maximum power (NG): kWm (bhp)	132 (177)	Heat rejection to coolant: kW (BTUM)	81.29 (4,623)
Maximum power (LP): kWm (bhp)	132 (177)	Heat radiated to ambient: kW (BTUM)	41.54 (2,362)
Steady state frequency band	C/F	Fan power: kW (hp)	4.1 (5.5)
Air cleaner	dry		
		Air requirements	
Liquid capacity			NG and LPG
Total oil system: L (gal)	5.7 (1.5)	Aspirating: *m³/min (SCFM)	5.91 (208.7)
Engine jacket water capacity: L (gal)	6 (1.6)	Air flow required for radiator	
System coolant capacity: L (gal)	27.47 (7.25)	cooled unit: *m³/min (SCFM)	254.9 (9,001.7)
		Remote cooled applications; air flow required for	
Electrical		dissipation of radiated generator set heat for a	
Electric volts DC	12	maximum of 25 °F rise: *m³/min (SCFM)	150.9 (5,329)
Cold cranking amps under -17.8 °C (0 °F)	925		
Batteries: group size	31	* Air density = 1.184 kg/m³ (0.0739 lbm/ft³)	
Batteries: quantity	1		
		Exhaust system	
Fuel inlet - vaporous supply			NG and LPG
Fuel supply connection size	1-1/2" NPT	Gas temperature (stack): °C (°F)	716.1 (1,321)
Fuel supply pressure: mm $H_2O$ (in. $H_2O$ ) 178–279 (		Gas volume at stack temperature: m³/min (CFM)	20.2 (713.4)
		Maximum allowable back pressure at	
Fuel inlet - liquid supply		outlet of engine, before piping: kPa (in. H <sub>2</sub> 0)	6.23 (25)
Fuel supply connection size #6 (3/8") fer	nale SAE 45° flare		
Maximum fuel supply pressure: kPa (PSI)	2,150 (312)		

#### Weights and dimensions





Drawing above for illustration purposes only, based on standard open power 480 volt generator set. Lengths may vary with other voltages. Do not use for installation design. See website for unit specific template drawings.

System	Dimensions (LxWxH)	Weight
Open Power Unit (OPU)	2,199 x 1,158 x 1,556 mm (86.6 x 45.6 x 61.3 in)	1,094-1,841 kg (2,411-4,059 lb)

Weights and dimensions are based on open power units and are estimates only. Consult the factory for accurate weights and dimensions for your specific generator set.

#### Sound data

Unit type	Standby full load (NG)	Standby full load (LP)
Level O (OPU): dB(A)	77.2	77.3

Sound data is provided at 7 m (23 ft). Generator set tested in accordance with ISO 8528-10 and with infinite exhaust.

#### **Emissions data**

Fuel type	THC + NO <sub>x</sub>	СО
Natural gas	0.44	0.2
Liquid propane	0.12	0.09

All units are in g/hp-hr and are EPA weighted cycle values.
Emission levels of the engine may vary with ambient temperature, barometric pressure, humidity, fuel type and quality, installation parameters, measuring instrumentation, etc. The data was obtained in compliance with US EPA regulations.

### Rating definitions and conditions

- Standby ratings apply to installations served by a reliable utility source. The standby rating is applicable to varying loads for the duration of a power outage. No overload capability for this rating. Ratings are in accordance with ISO 3046-1, BS 5514, and AS 2789. Average load factor: ≤ 85%.
- Nominal ratings at standard conditions: 25 °C and 300 meters (77 °F and 1,000 feet).
- Deration factor:
  - Consult your local *mtu* Distributor for altitude derations.
  - Consult your local *mtu* Distributor for temperature derations.

C/F = Consult Factory/*mtu* Distributor