



Diesel Generator Set

MTU 12V2000 DS800

800 kWe/60 Hz/Standby/208 - 4,160V

Reference MTU 12V2000 DS800 (725 kWe) for Prime Rating Technical Data

System ratings

Voltage (L-L)	208V † ‡	240V † ‡	380V † ‡	480V † ‡	600V ‡	4,160V
Phase	3	3	3	3	3	3
PF	0.8	0.8	0.8	0.8	0.8	0.8
Hz	60	60	60	60	60	60
kW	800	800	800	800	800	800
kVA	1,000	1,000	1,000	1,000	1,000	1,000
Amps	2,776	2,406	1,519	1,203	962	139
skVA@30% voltage dip	2,125	2,125	2,710	3,175	3,340	1,990
Generator model*	LSA 49.1 L11	LSA 49.1 L11	LSA 49.1 L8	LSA 49.1 L9	LSA 49.1 L9	LS 50.2 L5
Temp rise	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C	130 °C/40 °C
Connection	12 LEAD WYE	12 LEAD DELTA	6 LEAD WYE	6 LEAD WYE	6 LEAD WYE	6 LEAD WYE

* Consult the factory for alternate configuration.

† UL 2200 offered

‡ CSA offered

Certifications and standards

- Emissions
 - EPA Tier 2 compliant
- Generator set is designed and manufactured in facilities certified to standards ISO 9001:2008 and ISO 14001:2004
- Seismic certification – optional
 - IBC certification
- UL 2200 - optional (refer to *System ratings* for availability)
- CSA - optional (refer to *System ratings* for availability)
 - CSA C22.2 No. 100
 - CSA C22.2 No. 14
- Performance Assurance Certification (PAC)
 - Generator set tested to ISO 8528-5 for transient response
 - Verified product design, quality, and performance integrity
 - All engine systems are prototype and factory tested
- Power rating
 - Accepts rated load in one step per NFPA 110
 - Permissible average power output during 24 hours of operation is approved up to 85%.

Standard features*

- MTU is a single source supplier
- Global product support
- 2 year standard warranty
- 12V2000 diesel engine
 - 23.9 liter displacement
 - Electronic unit pump injection
 - 4-cycle
- Complete range of accessories
- Cooling system
 - Integral set-mounted
 - Engine-driven fan
- Generator
 - Brushless, rotating field generator
 - 2/3 pitch windings
 - AREP supply to regulator
 - 300% short circuit capability
- Digital control panel(s)
 - UL recognized, CSA certified, NFPA 110
 - Complete system metering
 - LCD display

Standard equipment*

Engine

- Air cleaners
- Oil pump
- Oil drain extension and S/O valve
- Full flow oil filter
- Closed crankcase ventilation
- Jacket water pump
- Inter cooler water pump
- Thermostats
- Blower fan and fan drive
- Radiator - unit mounted
- Electric starting motor - 24V
- Governor – electronic isochronous
- Base - structural steel
- SAE flywheel and bell housing
- Charging alternator - 24V
- Battery box and cables
- Flexible fuel connectors
- Flexible exhaust connection
- EPA certified engine

Generator

- NEMA MG1, IEEE, and ANSI standards compliance for temperature rise and motor starting
- Sustained short circuit current of up to 300% of the rated current for up to 10 seconds
- Self-ventilated and drip-proof
- Superior voltage waveform
- Digital, solid state, volts-per-hertz regulator
- No load to full load regulation
- Brushless alternator with brushless pilot exciter
- 4 pole, rotating field
- 130 °C maximum standby temperature rise
- 1-bearing, sealed
- Flexible coupling
- Full amortisseur windings
- 125% rotor balancing
- 3-phase voltage sensing
- ±0.25% voltage regulation
- 100% of rated load - one step
- 5% maximum total harmonic distortion

Digital control panel(s)

- Digital metering
- Engine parameters
- Generator protection functions
- Engine protection
- CANBus ECU communications
- Windows®-based software
- Multilingual capability
- Remote communications to RDP-110 remote annunciator
- Programmable input and output contacts
- UL recognized, CSA certified, CE approved
- Event recording
- IP 54 front panel rating with integrated gasket
- NFPA 110 compatible

Application data

Engine

Manufacturer	MTU
Model	12V2000G85TB
Type	4-cycle
Arrangement	12-V
Displacement: L (in ³)	23.9 (1,457)
Bore: cm (in)	13 (5.1)
Stroke: cm (in)	15 (5.9)
Compression ratio	16:1
Rated rpm	1,800
Engine governor	electronic isochronous (ADEC)
Maximum power: kWm (bhp)	890 (1,194)
Speed regulation	± 0,25%
Air cleaner	dry

Liquid capacity (Lubrication)

Total oil system: L (gal)	77 (20.3)
Engine jacket water capacity: L (gal)	110 (29.1)
After cooler water capacity: L (gal)	20 (5.3)
System coolant capacity: L (gal)	372 (98.3)

Electrical

Electric volts DC	24
Cold cranking amps under -17.8 °C (0 °F)	2,800

Fuel system

Fuel supply connection size	#12 JIC 37° male
Fuel return connection size	#12 JIC 37° male
Maximum fuel lift: m (ft)	3 (10)
Recommended fuel	diesel #2
Total fuel flow: L/hr (gal/hr)	480.7 (127)

Fuel consumption

At 100% of power rating: L/hr (gal/hr)	224 (59)
At 75% of power rating: L/hr (gal/hr)	168 (45)
At 50% of power rating: L/hr (gal/hr)	114 (30)

Cooling - radiator system

Ambient capacity of radiator: °C (°F)	50 (122)
Maximum restriction of cooling air: intake and discharge side of radiator: kPa (in. H ₂ O)	0.12 (0.5)
Water pump capacity: L/min (gpm)	833 (220)
After cooler pump capacity: L/min (gpm)	258 (68)
Heat rejection to coolant: kW (BTUM)	315 (17,914)
Heat rejection to after cooler: kW (BTUM)	270 (15,355)
Heat radiated to ambient: kW (BTUM)	82.1 (4,670)
Fan power: kW (hp)	34.5 (46.3)

Air requirements


Aspirating: *m ³ /min (SCFM)	66 (2,331)
Air flow required for radiator cooled unit: *m ³ /min (SCFM)	1,200 (42,400)
Remote cooled applications; air flow required for dissipation of radiated generator set heat for a maximum of 25 °F rise: *m ³ /min (SCFM)	300 (10,532)

* Air density = 1.184 kg/m³ (0.0739 lbm/ft³)

Exhaust system

Gas temp. (stack): °C (°F)	580 (1,076)
Gas volume at stack temp: m ³ /min (CFM)	174 (6,145)
Maximum allowable back pressure at outlet of engine, before piping: kPa (in. H ₂ O)	8.5 (34.1)

Weights and dimensions



Drawing above for illustration purposes only, based on standard open power 480 volt generator set. Lengths may vary with other voltages. Do not use for installation design. See website for unit specific template drawings.

System	Dimensions (L x W x H)	Weight (less tank)
Open power unit (OPU)	4,675 x 2,292 x 2,341 mm (184 x 90.2 x 92.2 in)	7,883 kg (17,379 lb)

Weights and dimensions are based on open power units and are estimates only. Consult the factory for accurate weights and dimensions for your specific generator set.

Sound data

Unit type	Standby full load
Level O: Open power unit: dB(A)	92

Sound data is provided at 7 m (23 ft). Generator set tested in accordance with ISO 8528-10 and with infinite exhaust.

Emissions data

NO _x + NMHC	CO	PM
4.66	0.45	0.01

- All units are in g/hp-hr and shown at 100% load (not comparable to EPA weighted cycle values). Emission levels of the engine may vary with ambient temperature, barometric pressure, humidity, fuel type and quality, installation parameters, measuring instrumentation, etc. The data was obtained in compliance with US EPA regulations. The weighted cycle value (not shown) from each engine is guaranteed to be within the US EPA Standards.

Rating definitions and conditions

- Standby ratings apply to installations served by a reliable utility source. The standby rating is applicable to varying loads for the duration of a power outage. No overload capability for this rating. Ratings are in accordance with ISO 8528-1, ISO 3046-1, BS 5514, and AS 2789. Average load factor: ≤ 85%.
- Consult your local MTU Distributor for derating information.