





Marine

DIESEL ENGINE 12V 4000 M63

for vessels with unrestricted continuous operation (1A)



Engine	Dimensions (L x W x H) mm (in)	Mass, dry kg (lbs)
12V / M63	2520 x 1850 x 2075 (99.2 x 72.8 x 81.7)	7240 (15961)
Engine with gearbox	Dimensions (L x W x H) mm (in)	Mass, dry kg (lbs)
12V / ZF W7640	4295 x 1850 x 2570 (169.1 x 72.8 x 101.2)	9675 (21329)



Typical applications: Work boats, tugs, barges, ferries, governmental vessels

Optional equipment and finishing shown. Standard may vary.

Engine type	12V 4000 M63	
Rated power ICFN	kW	1500
	(bhp)	(2012)
Speed	rpm	1800
Bore/stroke	mm (in)	170/210 (6.7/8.3)
Displacement, total	l (cu in)	57.2 (3491)
Flywheel housing	SAE 00	
Gearbox model, standard	WAF 763 L	
Gearbox model, alternative	ZF W7640	
Optimization of exhaust emissions ¹⁾	IMO II/EPA 2/EU IIIA ²⁾	

- 1) IMO - International Maritime Organisation (MARPOL)
- 2) Recognition through the RheinSchUO (CCNR)
EPA - US Marine Regulation 40 CFR 94 EU - EU Nonroad Directive 97/68/EC, Tier III A
M63 - heavy duty with high load factors up to approximately 80%

Fuel consumption ¹⁾		12V 4000 M63
Fuel consumption	g/kWh	201
on propeller curve ¹⁾	l/hr	363.3
	gal/hr	95.9

1) Tolerance +5% per ISO 3046, Diesel fuel to DIN EN 590 with a min L.H.V. of 42800 kJ/kg (18390 BTU/lb)

Standard equipment	
Starting system	Electric starter 24 V, 2 pole
Oil system	Gear driven lube oil pump, non switchable oil filter, centrifugal oil filter, lube oil heat exchanger, pump for lube oil extraction, opened crankcase ventilation
Fuel system	Fuel conditioning system with water separator, fuel delivery pump, duplex lube fuel filter with diverter valve, commonrail fuel injection system with high-pressure pump, pressure accumulator and electronic fuel injection with cylinder cutout system, jacketed HP fuel lines, flame- proof hose lines, leak-off fuel tank level monitoring
Cooling system	Engine version for separate heat exchanger, gear driven coolant circulation pump
Combustion air system	Dry charge air manifolds, engine coolant temperature-controlled intercooler, turbocharging with 2 water-cooled turbochargers, on-engine seawater-resistant air filters
Exhaust system	Triple-walled, liquid-cooled, on-engine exhaust manifolds, 30° discharge elbow, exhaust bellows
Mounting system	Resilient mounts
Power transmission	Torsional resilient and off-set compensating coupling (Centa CX for D-Drive); torsional resilient coupling with bearing housing (Centamax for T-Drive)
Auxiliary PTO	Charging generator, 120A, 28V, 2 pole
Engine management system	Engine control and monitoring system (ADEC); engine interface module-EiM, engine mounted
Engine safety system	The scope of delivery for the engine fulfils SOLAS requirements for admissible surface temperature and shielding of fuel and lube oil lines

Optional equipment	
Starting system	Coolant preheating system; air starter
Oil system	Lube oil priming system, oil level monitoring, automatic oil replenishment system with basic scope of monitoring, switchable oil filter with extended scope of monitoring
Fuel system	Switchable pre-filter with water separator in conjunction with switchable additional secondary filter
Cooling system	Coolant-to-raw water plate core heat exchanger, self priming centrifugal raw water pump, engine mounted coolant expansion tank, gear driven coolant circulation pump, raw-water connection for gearbox cooling
Combustion air system	Intake air silencer
Exhaust system	90° discharge elbow
Auxiliary PTO	Bilgepump (as secondary coolant pump), PTOs at free end of engine
Engine management system	Expansion In compliance with extended scope of monitoring (individual exhaust temperature monitoring)
Gearbox options	Various reserve reduction gearbox models, elec. actuated, gearbox mounts, PTO for hydraulic pump at driving shaft or at mediate shaft, trolling, trailing pump, propeller shaft flange
Classification	ABS, BV, CCS, CR, DNV, GL, KR, LR, NK, RINA including necessary extensions to scope of supply

Reference conditions:

- > Power definition according ISO 3046-1:2002 (E) and ISO 15550:2002 (E)
- > Intake air temperature 25°C/Sea water temperature 25°C
- > Intake air depression 15 mbar / Exhaust back pressure 30 mbar
- > Barometric pressure 1000 mbar
- > Power reduction at 45°C/32°C: none

Specifications are subject to change without notice.
All dimensions are approximate, for complete information refer to installations drawing. For further information consult your MTU distributor/dealer.