

Marine

DIESEL ENGINE 12V 2000 M41A/B

for on-board power generation and diesel-electric drives in continuous operation (3B)



Engine	Dimensions (L x W x H) mm (in)	Mass, dry kg (lbs)
M41 A/B	2105 x 1400 x 1290 (82.9 x 55.1 x 50.8)	2600 (5732)

16V picture



Optional equipment and finishing shown. Standard may vary.

Engine type		12V 2000 M41A 50 Hz	12V 2000 M41B 60 Hz	
Rated power ICXN	kW	575	695	
	(bhp)	(771)	(932)	
Speed	rpm	1500	1800	
No. of cylinders		12	12	
Bore/stroke	mm (in)	130/150 (5.1/5.9)	130/150 (5.1/5.9)	
Displacement, total	l (cu in)	23.9 (1458)	23.9 (1458)	
Flywheel housing		SAE O	SAE 0	
Exhaust optimization ¹⁾		IMO II	IMO II	
Solas compliance		Yes	Yes	

1) IMO - International Maritime Organisation (Marpol-convention)



Performance & fuel consumption ¹⁾		12V 2000 M41A	12V 2000 M41B
Speed	rpm	1500	1800
Maximum power	kW	575	695
	bhp	771	932
75% power	kW	431	521
	bhp	578	699
Fuel consumption	g/kWh	205	207
at 75% power	l/h	106.1	129.5
	gal/h	28.0	34.2

1) Tolerance +5% per ISO 3046, Diesel fuel to DIN EN 590 with a min L.H.V. of 42800 kJ/kg (18390 BTU/lb) All pumps necessary for engine operation included. Heat exchanger version without sea water pump: -2 g/kWh

Standard equipment			
Starting system	Electric starter 24 V		
Auxiliary PTO	Charging generator, 140A, 28V, 2 pole		
Oil system	Gear driven lube oil pump, lube-oil duplex filter with diverter valve, lube-oil heat exchanger, handpump for oil		
Fuel system	Fuel feed pump, fuel pre-filter, fuel main filter with diverter valve, on-engine fuel oil cooler, leak-off tank level monitored		
Cooling system	Coolant-to-raw water plate core heat exchanger, self priming centrifugal raw water pump, gear driven coolant circulation pump		
Combustion air system	Turbocharging with 2 water-cooled exhaust-gas turbochargers, on-engine intake air filters		
Exhaust system	Triple-walled, liquid-cooled, on-engine exhaust manifolds, twin exhaust outlet, exhaust bellows horizontal discharge, SOLAS Kit		
Mounting system	Resilient mounts at free end and driving end		
Electronics and instrumentation	Engine and gearbox control and monitoring system (MDEC)		
Optional equipment			
Starting system	Pneumatic starter		
Fuel oil system	Duplex fuel prefilter, fuel conditioning system		
Cooling system	Coolant preheating system, integr. seawater gearbox piping		
Exhaust system	Exhaust bellows vertical discharge		
Engine management system	In compliance with classification society regulations (EMU + MEU)		
Monitoring/control system	genoline		
Power transmission	Torsionally resilient coupling		

Reference conditions:

Power definition according ISO 3046
Intake air temperature 25°C/Sea water temperature 25°C

> Intake air depression 15 mbar/Exhaust back pressure 30 mbar

> Barometric pressure 1000 mbar

Specifications are subject to change without notice. All dimensions are approximate, for complete information refer to installation drawing. For further information consult your distributor/dealer.

Rolls-Royce Group www.mtu-solutions.com